



**Specification:** Stand-alone self-contained emergency LED downlight. Open area lens integrated. Constant emergency light (1.5W/200lm) for 3 hours. Low stand-by power consumption (0.5W). Self-test versions and remote controls available. Lithium battery as standard. Non-maintained configuration. Ceiling surface mount. Suitable for open area and corridor indoor applications.



\* Self-test only available on AST and PST versions

## Key Features

- Integrated test button
- Low stand-by power consumption (0.5 W)
- Fast battery re-charge (8 hours)\*
- Open area, corridor and spot lens options
- Remote control available

\* First battery charge takes up to 16 hours

## VISUAL Emergency Downlight

Part number **	Description	Testing facility	Remote control part number *	Operating temperature	Net weight
DLB1.5-OA2-MT	Ceiling mounted LED downlight NM 1.5W 200lm open area MT	Manual Test (MT)	ARC	0°C ~ 40°C	0.27 kg
DLB1.5-OA2-AST	Ceiling mounted LED downlight NM 1.5W 200lm open area Self Test AST	Advanced Self-Test (AST)	ARC		
DLB1.5-OA2-PST	Ceiling mounted LED downlight NM 1.5W 200lm open area Self Test PST	Programmable Self-Test (PST)	PRC		

\* Advance Remote Control (ARC) allows the accredited installer to carry out functional tests and/or full duration tests at any time and to check system's status. Please refer to ARC's user guide. In addition to ARC functions the Programmable Remote Control (PRC) allows the accredited installer to programme the testing schedule of each emergency luminaire. Please refer to PRC's user guide.

\*\*For Black option add -BLK to part number shown

# VISUAL Emergency Downlight

## Technical information

Input voltage/frequency	220-240V AC 50Hz
Power consumption	
Maintained	N.A.
Non-maintained	3W(Max.*) 0.5W(standby)
Lumen output	
On mains voltage	N.A.
On emergency mode	200lm
LEDs Lifetime (L-70)	50,000h
Discharge duration	3 hours
Wh (non-maintained standby)	0.5
Charge duration	up to 8hrs (first charge up to 16hrs)
Test facility	MT, AST, PST
IP rate	IP20
IK rate	IK06
Insulation class	II
Operation temp.	0~40°C
Storage temp.	0~50°C

## Light Source

Brand	Luminus
Quantity	1 pcs
CCT	4000K
CRI	>80

\* Power consumption only during charging mode

## Materials

Luminaire housing	Polycarbonate
Luminaire diffuser	Polycarbonate
Luminaire bracket	Polycarbonate
Luminaire legend	N.A.
Luminaire screws	Nickel Steel
Finish	Matt
Colour	White / Black
Battery type	Li-Ion 3.6V 2500mAh

## Logistic information

Product dimensions (L x W x D)mm	R75 x 40 mm
Product Net weight (kg)	0.27kg
Box dimensions (L x W x D)mm	160 x 154 x 50 mm
Gross weight (kg)	0.35kg
Quantity of outer carton	28 pc's
Outer carton dimensions(L x W x D)mm	360 x 336 x 327 mm
Outer carton gross weight (kg)	11.5kg
Quantity per Euro pallet (1200 x 800)	672 pc's
Pallet weight (kg)	10 kg

## Certification

Safety standard	BS EN 60598-2-22
Certified by	DEKRA
UKCA / CE / ENEC mark	Yes
Factory QMS	ISO9001

## Installation Notes

- Surface ceiling mount
- Cable entry to side (20mm cut-out) and rear
- Screwless terminal block (L, N, earth loop in/out)
- Terminal block takes wires up to 3 x 2.5mm<sup>2</sup>

## TESTING FACILITIES

MT (Manual Test)	This luminaire needs to be tested by a competent person according to BS EN 50172:2004. This luminaire can be used in conjunction with the Advanced Remote Control (ARC). ARC is an optional tool that adds new features to AST and MT emergency luminaires. If functional test or full duration test is initiated via ARC the MT luminaire will automatically switch to mains mode after the functional or full duration test is completed.
AST (Advanced Self-Test)	This is a self-test luminaire. Functional test is carried out automatically once a week and runs for 30 seconds. Full duration test is carried out automatically every 52 weeks. First full duration test is carried out automatically within the first 4 weeks after the luminaire being connected to mains voltage. This luminaire can be used in conjunction with the Advanced Remote Control (ARC). ARC is an optional tool that adds extra features to AST emergency luminaires. Please refer to the ARC's user guide.
PST (Programmable Self-Test)	This is a programmable self-test luminaire. It must be used in conjunction with a Programmable Remote Control (PRC). Please refer to PRC's user guide.